



# Care Slimline

## 90° LEFT-HAND RAIL

### Features

- Soft square bracket design
- Manufactured to comply with relevant accessible grab rail requirements for AS 1428.1:2021 Access and Mobility
- Designed to withstand a force of 1100N (112 kg) in any directions
- Made from 304 stainless steel
- Concealed fixings
- Wall mounting screws included

**Please Note:** Suitable support must be included behind the wall for fixing bolts.



### Available in

- |   |   |   |
|---|---|---|
|   |   |   |
| Polished<br>Stainless Steel<br><b>FC8357L-C</b>                                     | PVD<br>Matte Black<br><b>FC8357LMB-C</b>  | PVD<br>Brushed Nickel<br><b>FC8357LBN-C</b>   |
|  |  |  |
| PVD<br>Gun Metal<br><b>FC8357LGM-C</b>  | PVD<br>Brushed Copper<br><b>FC8357LCO-C</b>   | PVD<br>Urban Brass<br><b>FC8357LUB-C</b>  |

### Cleaning & Care

- Regularly clean with mild soapy water using a microfibre cloth.
- In highly polluted or coastal locations, we recommend cleaning 2-3 times per week.
- Do not use harsh detergents, bleach, cream cleaners or citrus based cleaners. These substances are abrasive and will damage the surface.
- Do not use undue pressure and wipe in one direction only.

We aim to ensure that specifications are correct at the time of publication. All measurements are shown in millimetres. Always use measurements of actual product received for final specification as the technical drawing may contain differences. Due to printing limitations, physical colour may vary from the image shown. Fienza reserves the right to make modifications without prior notice.